

Indoor Cabling Components

Flexible PA duct

APPLICATION:

Protective flexible conduit with a high mechanical strength.

FEATURES:

- Easy to install, bending radius as low as 25 cm
- Robust, high crush resistance
- Meet requirements acc. to UL and NEN 50086



CONSTRUCTION:

Flexible protective duct flame retardant, zero halogen and zero cadmium.

Components

Duct	Diameter Inner / outer (mm)	Duct Colour	Packing unit	Ordering code
N12	12.0 / 15.8	Black	Coil 50 meter	1013639
N17	16.2 / 21.2	Black	Coil 100 meter	1013641
N23	22.6 / 28.5	Black	Coil 100 meter	1013642
N29	29.0 / 34.5	Black	Coil 100 meter	1013643
	--- / 14.0	Black	Coil 30.5 meter	1017103