

# Indoor Cabling Components

## Optical fibre protection tube (miniflex)

### APPLICATION:

Used in any fibre application where enhanced protection is necessary.

### FEATURES:

- Offers superior protection for fibre cable
- Reduces transient losses due to microbend
- Bend radius limiting from 10 to 50 mm
- Ideal for cabled fibre in MDU's and blown fibre applications

### CONSTRUCTION:

The tube is made of Nylon PA 12  
 Temperature range - 40 °C to + 110 °C  
 High chemical resistance  
 Low smoke halogene free  
 Flame retardancy according to UL94/V2



## Components

Diameter Outer / inner (mm)	Pull-cord	Duct Colour	Packing unit	Ordering code
3.0/1.4	No	White	Drum 100 meter	<b>1018503</b>
4.0/2.4	No	White	Drum 100 meter	<b>1018504</b>
5.0/3.1	No	White	Drum 100 meter	<b>1018505</b>
5.0/3.1	Yes	White	Drum 100 meter	<b>1027758</b>

Diameter Outer / inner (mm)	Pull-cord	Duct Colour	Packing unit	Ordering code
3.0/1.4	No	White	Drum 1000 meter	<b>1018506</b>
4.0/2.4	No	White	Drum 1000 meter	<b>1018507</b>
5.0/3.1	No	White	Drum 1000 meter	<b>1018508</b>
5.0/3.1	Yes	White	Drum 1000 meter	<b>1027759</b>