

## 19" / ETSI Racks

**Prysmian Part Numbers: *See page 2***



The 19" / ETSI racks are standard racks for optical fibre distribution. The racks are available in heights of 42U (2000mm) and 47U (2200mm), and are able to accommodate a range of distribution equipment including Splicing and Patching Shelves and Distribution Sub-Racks. The racks are supplied fully built with a frame, side and rear panels, doors and a brushed roof for patch cord routing. The racks can be supplied empty or Prysmian can install a range of its Rack Mounted Products prior to shipment.

### Features and Benefits

- Racks are available in 42U or 47U heights.
- They can be supplied configured with either 19" or ETSI mounting rails.
- Double depth racks (600mm) are available for increased capacity, allowing modules to be arranged back to back.
- Steel or glass doors can be supplied as requested.
- Brushed exit roofs are supplied for patch cord routing.
- Supplied fitted with a three point lock bar and lever handle.
- Can be supplied pre-fitted with Prysmian Rack Mounted Products.

### Kit Contents

- Rack Frame
- Rear Panel
- Side Panels
- Door
- Roof

### Additional Items - Optional

- Baying Kit

## Technical Data

- Required space envelope (mm):
 

42U standard:	(w) 600 x (d) 300 x (h) 2000
42U double depth:	(w) 600 x (d) 600 x (h) 2000
47U standard:	(w) 600 x (d) 300 x (h) 2200
47U double depth:	(w) 600 x (d) 600 x (h) 2200
- Materials: Mild Steel
- Finish: Painted Light Grey (RAL 7035)

## Logistics

- Packing Dimensions (mm):
 

42U and 47U standard:	(w) 680 x (d) 360 x (h) 2280
42U and 47U double depth:	(w) 680 x (d) 660 x (h) 2280
- Weight (kg):
 

42U packed:	Approx 170	Net: Approx 100
47U packed:	Approx 180	Net: Approx 110

## Part Numbers

Part Number	Description
XEXSC00310	19" Rack – Steel Door – 2000 (42U) x 600 x 600
XEXSC00311	19" Rack – Steel Door – 2000 (42U) x 600 x 300
XEXSC00312	19" Rack – Steel Door – 2200 (47U) x 600 x 600
XEXSC00313	19" Rack – Steel Door – 2200 (47U) x 600 x 300
XEXSC00314	ETSI Rack – Steel Door – 2000 (42U) x 600 x 600
XEXSC00315	ETSI Rack – Steel Door – 2000 (42U) x 600 x 300
XEXSC00316	ETSI Rack – Steel Door – 2200 (47U) x 600 x 600
XEXSC00317	ETSI Rack – Steel Door – 2200 (47U) x 600 x 300
XEXSC00318	19" Rack – Glass Door – 2000 (42U) x 600 x 600
XEXSC00319	19" Rack – Glass Door – 2000 (42U) x 600 x 300
XEXSC00320	19" Rack – Glass Door – 2200 (47U) x 600 x 600
XEXSC00321	19" Rack – Glass Door – 2200 (47U) x 600 x 300
XEXSC00322	ETSI Rack – Glass Door – 2000 (42U) x 600 x 600
XEXSC00323	ETSI Rack – Glass Door – 2000 (42U) x 600 x 300
XEXSC00324	ETSI Rack – Glass Door – 2200 (47U) x 600 x 600
XEXSC00325	ETSI Rack – Glass Door – 2200 (47U) x 600 x 300
<b>Other Accessories</b>	
XEXSG00303	Baying Kit

Please contact your local sales office listed on [www.prysmiangroup.com](http://www.prysmiangroup.com)

© Prysmian Group 2012, All Rights Reserved.  
The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.