Draka

Draka Comteq | Cable Solutions EMEA

Duct system outside plant
Microducts 7, 10 and 12 mm shape retaining

APPLICATION:
The "OverGlide" microducts are designed for jetting into plastic protective ducts under outside plant conditions. Their special shape retaining properties allow blowing of very tight fitting cables.

FEATURES:

- Superior characteristics for jetting microducts into duct, extra high outside pressure resistance, reducing risk of implosion
- Jetting parameters stable over long period of time (> 15 years)
- Superior characteristics for jetting tight fitting cables into microduct, high pressure resistance
- Robust, having extra high crush resistance

MATERIAL:
Special grade HDPE plastic, having low friction coefficient and high Young's modulus.



Types:	12 mm	10 mm	7 mm	
Innerdiameter	9.6	8.0	5.5	mm
Outer diameter	12.0	10.0	7.0	mm

Types (ordering code)

Colour	Red	White	Yellow	Blue	Green	Violet
12 mm	**1016352**	**1016353**	**1016354**	**1016355**	**1016356**	**1016357**
10 mm	**1016339**	**1016341**	**1016342**	**1016343**	**1016344**	**1016345**
7 mm	**1016326**	**1016327**	**1016328**	**1016329**	**1016330**	**1016331**
Colour	**Brown**	**Black**	**Orange**	**Turquoise**	**Grey(slate)**	**Pink(rose)**
12 mm	**1016358**	**1016359**	**1016360**	**1016361**	**1016362**	**1016363**
10 mm	**1016346**	**1016347**	**1016348**	**1016349**	**1016350**	**1016351**
7 mm	**1016332**	**1016334**	**1016335**	**1016336**	**1016337**	**1016338**

Packing and installation properties

Duct type	Standard length m	Drum size Flange / width / core cm	Pulling force N	Max. inner pressure at 20° C for 30 min bar	Max outer pressure at 20° C for 60 min bar
12 mm		100/50/50	180	15	10
10 mm	2000	100/50/50	125	15	10
7 mm		100/50/50	60	15	10

Length tolerance +/- 1 % Sealing of microducts: End caps

Marking

Each microduct is marked at intervals of 1 metre with:	**Draka XS-net OverGlide** date of manufacture length marking

No communication and reproduction without written authorisation

Duct system outside plant
Microducts 7, 10 and 12 mm shape retaining

No communication and reproduction without written authorisation