




Click-Fit[®] Joints



Accessories for high voltage
polymeric cables

About us

Prysmian is a world leader in the energy and telecommunication cables industry with a strong market position in higher added value market segments.


It is organised in two business sectors - Energy Cables & Systems (submarine and underground cable systems for power transmission and distribution, cabling solutions for residential and infrastructure buildings and cabling systems for signalling, control and power feeding for a wide range of industrial applications) and Telecom Cables & Systems (optical fibres, optical cables and copper cables for voice, video and data transmission). The Prysmian Group has a global presence in 34 countries with 54 plants, 7 international R&D Centers and more than 12,000 employees.

Specialising in the development of bespoke products and systems, Prysmian's main competitive strengths include: focus on research and development, ability to innovate in terms of both products and processes, and the use of advanced proprietary technologies.

Prysmian started manufacturing insulated cables for electric power distribution around 1880 and soon afterwards initiated the development of the first cable accessories.

Prysmian's very long and successful experience in HV and EHV cable systems have lead to the development of a comprehensive range of accessories for extruded dielectric cables.

A relentless R&D effort focused on rubber compounds as well as on electrical design has created accessories for all applications, based on pre-moulded and factory tested joint sleeves and termination stress cones that are recognised worldwide for their unsurpassed reliability.



CLICK-FIT®

> Concept

The CLICK-FIT® plug-in concept is a unique system designed to connect high and extra high voltage extruded power cables for 72kV up to 420kV. Following the principle of the CLICK-FIT® concept, the ends of the cables are prepared and provided with plugs. The uniform plug design enables the installation of joints and terminations simply by plugging-in the prepared cable end. Important features of the CLICK-FIT® concept are: high reliability combined with fast, easy and man-independent installation techniques, that lead to a reduction in project realization time and cost.

> Joint

The CLICK-FIT® joint is a prefabricated and pre-tested joint, designed to connect two high voltage cables with extruded insulation. The cable ends, provided with CLICK-FIT® plugs, are pushed into the silicone rubber insulating body and connected in the middle by means of silver plated electrical contacts. In the middle of the joint an integrated metallic grooved ring locks the position of the plugs through a spring-loaded bayonet mechanism. The CLICK-FIT® plug is connected by means of compression, MIG-welding or shear-off bolts.

The pre-moulded insulating and stress control body is made of high quality pre-moulded silicone rubber material with excellent insulating properties and high mechanical reliability. The integrated semi-conductive silicone rubber stress control cones and shielding electrode ensure a smoothly distributed electrical field control. The CLICK-FIT® locking mechanism connects both conductors and provides a core lock inside the joint.

Depending on the cable construction, different options are available to electrically re-connect the metallic cable sheaths or wire screens. A galvanized copper joint tube, polymeric shrinkage bodies or a combination of these provides protection of the joint against moisture ingress and external damages. The joint is fully submersible in water. Optionally, a polyester protective casing reinforced with glass fibre and filled with bitumen or polymeric compound is available. Straight joints as well as joints with integrated screen interruption for cross bonding purposes are available. In case of screen interruption, the metal joint casing is provided with an epoxy-insulating ring.

Factory prepared

> CLICK-FIT® cable ends

The so-called "Factory prepared CLICK-FIT® cable end" is a unique feature of the CLICK-FIT® concept. It allows cable preparation to be completed entirely in the cable factory. After assembly, the plug can be tested electrically together with factory testing of the cable reel. During transportation and pulling of the cable, the factory prepared plug is to be protected using the special CLICK-FIT® pulling eye.

The pulling eye includes a sturdy - yet flexible - hose that protects the cable and the plug from mechanical damages and water ingress. On site, the pulling eye is removed and the plug is inserted into the accessory. The plugs automatically lock into the joint body by using spring driven bayonets. The right connection is a fact!

Test and qualification program

The CLICK-FIT® joint has been subjected to comprehensive tests, comprising:

- > Electrical routine test on each individual joint body
- > Type tests according to IEC 60840, IEC 62067, NEN 3629 and IEEE 404
- > Prequalification tests according to IEC 62067
- > Short circuit tests
- > Dielectric withstand tests for AC and impulse voltages
- > Tests to ensure the compatibility between cable and accessories under different installation conditions

Prysmian HV Accessories quality system complies with both ISO 9001 and ISO 14001 standards. Prysmian HV accessories based on prefabricated mouldings represent a highly reliable solution that is considered a key component in the safe operation of a HV cable system.



Prefabricated CLICK-FIT® Joints

available from 72,5 kV up to 525 kV

> Additional features

Following the latest developments in cable design and in view of a full system approach, upon request the CLICK-FIT® joints can include:

- > Optical fibres management
- > Partial discharge sensor
- > Factory prepared CLICK-FIT® cable ends
- > Provisions to connect two extruded cables of different type and size

> Installation basics


- > Assembly of the CLICK-FIT® plug
- > Cable ends plugged into the joint body with the special hydraulic driven CLICK-FIT® installation frame
- > Connection of the cable metal screen
- > Application of the outer protective covering

> CLICK-FIT® joint characteristics

- > High quality and reliability
- > Prefabricated
- > Pre-tested joint body
- > CLICK-FIT® plug-in concept
- > Complying with IEC 60840, IEC 62067, NEN 3629 and IEEE 404
- > Copper casing ensures mechanical protection and absolute water tightness
- > Core locking mechanism

> Installation characteristics


- > Quick, easy and man-independent
- > Modular design allows tailor-made solutions
- > Locking the conductor in the joint body
- > Compact design, allowing installation in small spaces
- > Easy to handle, light-weighted tools



Legend

- 1 Plugs
- 2 CLICK-FIT® locking mechanism
- 3 Joint body
- 4 Shielding electrode
- 5 Stress control cones
- 6 Different options for covering

YOUR ENERGY... OUR SYSTEMS... ANYWHERE




Factory prepared cable end with pulling eye



Factory prepared cable end ready for installation



On-site cable end preparation




Cable end plug-in using installation frame



Joint core finishing



Complete joints in final position



ARGENTINA

Prysmian Energía Cables y Sistemas de Argentina S.A.
Fábrica La Rosa, Av.da Argentina 6784,
1439 Capital Federal
tel. +54 11 4630 2000
fax +54 11 4630 2100

AUSTRALIA

Prysmian Power Cables & Systems
Australia PTY LTD
1 Heathcote Road, Locked Bag 7042,
Liverpool Business Centre 1871, NSW
tel. +61 2 9600 0777
fax +61 2 9600 0747

AUSTRIA

Prysmian OEKW GmbH
Lembockgasse 47A,
1230 Wien
tel. +43 1 8667 70
fax +43 1 8667 7109

BRAZIL

Prysmian Energia Cabos e Sistemas do Brasil S.A.
Av. Alexandre de Gusmao 145,
09110-900 Santo André – SP
tel. +55 11 4998 4000
fax +55 11 4998 4811

CHINA

Prysmian Cables & Systems
1505-06, Tower A, City Center of Shanghai,
No. 100 ZunYi Road, Shanghai 200051
tel. +86 21 6237 1411
fax +86 21 6237 1195

EGYPT

Prysmian Cables & Systems
8 Abd El Azim Aoudallah st. Hegaz sq.,
Heliopolis – Cairo
tel. +20 2 2418 557
fax +20 2 6381 327

FINLAND

Prysmian Cables & Systems Oy
P.O. Box 13,
FIN-02401 Kirkkonummi
tel. +358 10 77551
fax +358 9 2982204

FRANCE

Prysmian Energie Cables et Systèmes
France s.a.
Zone Industrielle du PORT AU VIN,
GRON, 89 100 SENS
tel. +33 3 8695 7769
fax +33 3 8695 7781

GERMANY

Prysmian Kabel und Systeme GmbH
Alt-Moabit 91 D
10599 Berlin
tel. +49 30 3675 40
fax +49 30 3675 4640

HONG KONG

Prysmian Cable Systems Pte. Ltd.
Unit A, 18/F, China Overseas Building,
139 Hennessy Road, Wanchai, Hong Kong
tel. +85 2 2827 8308
fax +85 2 2827 7212

HUNGARY

Prysmian MKM Magyar Hungarian Cable
Works Co. Ltd.
Barázda u. 38, H-1116 Budapest
tel. +36 1 3822 222
fax +36 1 3822 202

INDONESIA

PT. Prysmian Cables Indonesia
Gedung BRI II, Suite 1502,
Jln. Jend Sudirman No 44-46,
Jakarta 10210
tel. +62 264 351 222
fax +62 264 351 780

ITALY

Prysmian Cavi e Sistemi Energia Srl
Viale Sarca 222, 20126 Milano
tel. +39 02 6449 9492
fax +39 02 6449 5035

KUWAIT

Prysmian Cables & Systems – Kuwait Office
Villa No 4 (next to Hyatt Regency Hotel),
Bidda – KUWAIT
tel. +965 575 7704
fax +965 572 5780

MALAYSIA

Prysmian Cable Systems Pte. Ltd.
Power Cable Malaysia Sdn Bhdn
Lot 2 Jalan Kawat 15/18
40702 Shah Alam, Selangor Darul Ehsan
tel. +60 3 5518 4528
fax +60 3 5511 9590

NETHERLANDS

Prysmian Cables and Systems B.V.
Schieweg 9, 2627 AN Delft
P.O. Box 495, 2600 AL Delft
The Netherlands
tel. +31 15 260 5260
fax +31 15 261 3808

NORTH AMERICA

Prysmian Cables & Systems North America
700 Industrial Drive,
Lexington, SC 29072 – USA
tel. +1 803 9511 130
fax +1 803 9511 092

ROMANIA

Prysmian Cabluri si Sisteme SA
Soseaua Draganesti, Km. 4,
0500 Slatina
tel. +40 49 435 699
fax +40 49 433 484

RUSSIA

Prysmian Cables and Systems
6th street 8 Marta, 6a, bldg 1
Moscow 125167
tel. +7 095 9337036
fax +7 095 9337035

SINGAPORE

Prysmian Cable Systems Pte. Ltd.
No 4 Tuas Avenue 12. 3rd Storey,
639047 Singapore
tel. +65 6862 9866
fax +65 6862 9877

SLOVAKIA

Prysmian Kablo s.r.o.
Trnavska cesta 50
821 02 Bratislava
tel. +421 2 4949 1215
fax +421 2 4949 1248

SPAIN

Prysmian Cables y Sistemas S.L.
Carretera C-15, Km. 2,
08800 Vilanova i la Geltrú (Barcelona)
tel. +34 93 811 6181
fax +34 93 811 6011

SWEDEN

Prysmian Kablar och System AB
Turebergs Allé 2
SE-19162 Sollentuna
tel. +46 8 260416
fax +46 8 260413

THAILAND

Prysmian Cable Systems Pte. Ltd.
555 RASA Tower 11th floor,
Phaholyothin Road,
Lardyao, Chatuchak,
Bangkok 10900
tel. +66 2 9370 316
fax +66 2 9370 318

TURKEY

Turk Prysmian Kablo ve Sistemleri A.S.
Buyukdere Caddesi No 117,
34394 Gayrettepe, Istanbul
tel. +90 212 3551 500
fax +90 212 2175 810

U.A.E. (Dubai)

Prysmian Cables and Systems Middle East
P.O. Box 72125
Dubai
tel. +971 4 345 7870
fax +971 4 345 7101

UK

Prysmian Cables and Systems Ltd.
Chickenhall Lane, Eastleigh,
Hampshire, SO50 6YU
tel. +44 2380 2955 55
fax +44 2380 2951 11