

RetractaNet^{XS} TBE-I2 Tapping Box

Prysmian Part Number: XJTSC01350



The RetractaNet^{XS} TBE-I2 Tapping Box is used to breakout and distribute the fibres from an in-line RetractaNet cable into drop tubes, for routing to a customer premises. It is UV resistant and sealed to IP68, enabling it to be mounted in the outdoor environment. It has the capacity to accommodate an in-line RetractaNet cable of up to 15mm in diameter. It enables a window to be cut in the cable to access the fibres, which can be spurred of into a drop tube of up to 7mm in diameter.

Features and Benefits

- Can accommodate an in-line RetractaNet cable from 10mm to 15mm in diameter.
- Can accommodate two drop tubes / cables of up to 10mm in diameter.
- Easy to install mechanical system using Gel to provide a seal to IP68.
- Suitable for direct buried applications.
- Impact and crush resistant.
- UV resistant for external use.
- Non craft sensitive and reliable.

Kit Contents

- TBE-I2 Tapping Box
- 3x Foam Tape 150mm x 10mm
- 4 Cable Ties 3.6mm x 150mm
- Installation Flysheet.

Additional Items

- Rubber seal

Technical Data

• Dimensions	190 x 72 x 32 mm
• Colour	Black
• Material	Polypropylene
• Temperature range:	
• Transport and storage	-10°C to +50°C
• Installation	-10°C to +50°C
• Operation	-20°C to +60°C
• Number of Cable Entries:	1 in-line, 2 Drops
• In Line Cable Diameter (mm):	10.0 to 15.0
• Drop Cable Diameter (mm):	6.0 to 10.0
• Fibre bending radius (mm):	minimum 15 (ITU-T G.657 A2 fibre)
• Cable retention:	15 mm cable: 350 N 7 mm drop tube: 150 N
• Water immersion:	IP68 (No water ingress at 1 meter water pressure for 7 days)
• Impact resistance	10 Nm @ 20 °C, radius 200 mm
• Crush resistance	1000 N @ 20 °C on top surface of the box
• Application area	Group 1 according to EN 124, placed minimum 25 cm below surface level Group 2 according to EN 124, placed minimum 30 cm below stone or concrete pavement

Logistics

• Packing Dimensions (mm):	(l) 210 (w) 160 (d) 28
• Packed Weight (kg):	0.176
• Net weight (kg):	0.130

Additional Items

Rubber Seal

The rubber seal wrap-around 3.5/1.25 is used to seal the space between drop tubes with an inner diameter of 3.5 mm and a fibre module of diameter 1.25 mm. The seal provides a tension relief on the fibre module. The seal has a longitudinal slit to enable wrap-around mounting after the fibre module is installed in the drop tube.



Prysmian Part No. – XBFSC01380

Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2014, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.