



Sirocco Tubes (External) - Direct Bury Anti-Rodent Assembly

Prysmian Part Number: See Table Below



Empty small diameter HDPE low friction tubes for blown fibre installation where rodent protection is required.

- Rapid dedicated customer connect using proven mechanical protection of HDPE.
- Low friction internal coating for maximum fibre blowing distance.
- 5 mm O/D, each tube accommodates up to a 12 fibre unit.
- Recommended for high tensile re-enforcement to reduce elongation under load, also providing resistance to rodent attack.
- Aluminium layer acts as moisture barrier.
- Can be customised to suit user requirements (e.g. tube style, sheath colour, print legend).
- Supplied on wooden drums containing either one length of tube or multiple lengths for simultaneous installation.
- External versions available in different constructions – direct install, direct bury, steel armour, anti-termite, anti-rodent.

Assembly of tubes surrounded by an aluminium moisture barrier, an inner polyethylene sheath, high tensile reinforcement layer and an outer polyethylene sheath.

Assembly type	Product Code	Nominal O.D. (mm)	Aluminium Sheath	Ripcord Qty	Min. Bend Radius (mm)	Max. Tensile (N)	Nominal Weight (g/m)	Drum Lengths (m)	
1 Way	OMR0501	12.7	150	1	336	1740	131	500m D*	2000m R
								1000m R*	4000m R
2 Way	OMR0502	12.7 x 17.7	150	1	336	2640	185	500m D	2000m R
								1000m R	4000m R
4 Way	OMR0504	19.8	150	1	510	3300	256	500m D	2000m R
								1000m R	4000m R
7 Way	OMR0507	23.3	150	1	600	4800	343	500m D	2000m R
								1000m R	4000m R
12 Way	OMR0512	30.7	150	1	720	5400	564	1000m R	3000m R
								2000m R	
19 Way	OMR0519	35.5	150	1	876	6600	714	1000m R	
								2000m R	
24 Way	OMR0524	40.1	150	1	1020	7200	869	1000m R	
								2000m R	
*D = Disposable Drum		*R = Returnable Drum							

Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2006. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Issue 01, July 2006
Ref: ST008-01